

TRITIUM COLLECTION SYSTEM F&J MODEL TCS-3000-BL

NOTABLE FEATURES:

- Microprocessor controlled electronics
- Flow rate measurements and volume totalizations are corrected to a factory settable reference Temperature and Pressure (4 options)
 Classical STP
 Normal T and P
 Modified Normal T and P
 Standard Ambient T and P
 Standard Ambient T and P
- ➢ RS-232 Port
- LED Display
- Precision machined orifice
- > Flow rate accuracy within $\pm 4\%$ F.S.
- Flow rate / volume options: sccm / scc SLPM / SL
- ➤ 100-120VAC; 50/60Hz, single phase
- Brushless motor

GENERAL DESCRIPTION:

The Model TCS-3000-BL Tritium Collection System is a tritium collection system consisting of a diaphragm pump, a brushless DC motor, automatic flow control and 2 removable polycarbonate Indicating Silica Gel columns. The flow and volume of air passing through the system is adjusted and measured by a microprocessor controlled Digital Flow Meter (DFM). The DFM utilizes a precision-machined orifice to measure flowrate. The DFM displays on-board calculations on a bright large character LED display. Flowrate and totalized volume are both corrected to a reference T and P. Elapsed time, flowrate and volume are displayed at operator selection.

Multiple operator selectable data download frequencies are available through the RS232 port for collection and/or storage of real-time data.

The unit is designed for continuous indoor use. Please consult the product specifications for the design temperature range and the installation category.

The typical operating flow range is 100 - 400 sccm (0,10 - 0,4 SLPM).



(h) (f)

SPECIFICATIONS: PUMP TYPE:	Diaphragm		
MOTOR:	Brushless; 12VDC		
CAPACITY:	Maximum capacity dependent upon pump size and flow sensor design.		
POWER REQUIREMENTS:	100-120VAC; 50/60 Hz; 1 ampere; single phase		
CIRCUIT BREAKER PROTECTION:	1 ampere		
ELECTRICAL CORD:	All temperature, 3-wire, 16 gauge; ~9 feet		
DIMENSIONS:	$9"D \times 24"W \times 20"H$		
WEIGHT:	67 lbs. (30,3 kg)		
INSTALLATION CATEGORY:	Pollution Degree 2		

ELECTRONIC SPECIFICATIONS

MEASUREMENT ACCURACY

Air flow:	$\pm 4\%$ of full	scale	
Temperature:	$\pm 0.9^{\circ}F$	(0.5°C)	(Not displayed)
Barometric Pressure:	± 0.6 inches	Hg	(Not displayed)

OPERATING TEMPERATURES:	0° - 104°F	(-17° - 40°C)*
STORAGE TEMPERATURE:	- 20° - 122°F	(-28° - 50°C)

STORAGE TEMPERATURE:	- 20° - 122°F	(-28° - 50
* With optional heating system		

with optional heating system

CALIBRATION: Calibration-verification once per year; Factory calibration as needed.

COMMUNICATIONS INTERFACES: RS-232

ON-BOARD CALCULATIONS

- > Flow calculation from differential pressure value corrected to a reference T and P
- ➢ Elapsed Time
- > Cumulative Volume corrected to a reference T and P

OPTIONS:

- FlashCard Datalogger system for collection and storage of real-time data exiting the RS232 port.
- FlashCard data storage device: P/N: 232FCDSD
- ➢ FlashCard 2 GB; P/N: 372239
- FlashCard Reader; P/N: SDDR-199-A20

NOTE:

Other tritium absorbing media may be utilized, such as molecular sieve, water or ethylene glycol.

F&J SPECIALTY PRODUCTS, INC. TEL: 352/680-1177 • FAX: 352/680-1454 • EMAIL: fandj@fjspecialty.com